


出血3mm  
成品版面尺寸: 80\*80mm

83mm

80mm

## USER MANUAL




Please read the user manual carefully before using the product and keep it properly

### Package


Please check and see if all the items are complete



### Appearance



### Video ports



Power  
3.5mm Audio  
USB 3.0 (TYPE B)

### Instructions


#### •Power on the camera

Plug in the power according to the installation diagram, connect the USB3.0 cable to the PC, the breathing light rotates in color, indicating that the power is turned on and self-test is completed. Then open the conference software and check whether there is video.

#### •How to use the product

According to the instructions of the IR remote control, control the lens according to the requirement, open the conference software and start the audio and video conference.

### Instruction of remote control



### Button instructions

- If the button doesn't respond, please check if the positive and negative pole of battery is correct, and check the battery lifespan
- Preset position: press the preset button for 3 seconds, it will take effect
- Call presets: shortly press the preset 1 or 2 button

### Breathing light status description

- MIC is muted, the breathing light always shows yellow and green
- Speaker is muted, the breathing light always shows pink
- MIC & speaker are muted at the same time, the breathing light always shows red
- When the MIC is switched to external MIC, the breathing light always shows blue

### •Specifications

Image Sensor	4K 1/2.5 CMOS sensor
Video Signal	4K、1080P、720P
Video Output	USB3.0, compatible with USB2.0
Horizontal View Angle	100° wide view angle
Preset Position	2 camera preset positions
Color Space Compression	MJPEG/YUY2/H.264
Power Consumption	DC 12V/1.5A
Interface	USB3.0(TYPE-B), compatible with USB2.0
Audio	Built in MIC and speaker, 3.5mm audio port
Dimension	400*70*45mm
Weight	950g